

DECLARATION

We, HOYA Medical Singapore Pte. Ltd., located at 455A Jalan Ahmad Ibrahim, Singapore 639939, hereby certify that the water absorption rates for the optical portion of our hydrophobic acrylic HOYA intraocular lenses are as follows:

AF-1 1-piece and 3-piece Clear lenses	Water Absorption Rate at Immersion Temperature
PC-60R	0.21% at 23°C
PC-60AD	0.21% at 23°C
150	0.21% at 23°C
250	0.21% at 23°C
254	0.21% at 23°C
NC1-SP	0.21% at 23°C

1. vandens kiekis 0,21%

AF-1 1-piece and 3-piece Yellow lenses	Water Absorption Rate at Immersion Temperature
PY-60R	0.25% at 23°C
PY-60AD	0.25% at 23°C
151	0.25% at 23°C
251	0.25% at 23°C
255	0.25% at 23°C

Vivinex Family lenses	Water Absorption Rate at Immersion Temperature
XC1	0.6% at 23°C
XY1	0.6% at 23°C
XC1-SP	0.6% at 23°C
XY1-SP	0.6% at 23°C

1. Vandens kiekis medžiagoje (įgeriamumas)



Eric Hoe
Director, Global QA Operation & R&D
HOYA Medical Singapore Pte. Ltd.

29-Jul-2020

Date