


Accessories for Insufflation

Veress-Needles and Accessories



- ① **A5150.1** Needle, according to Veress, 150 mm
- 05151.1** Needle, according to Veress, 120 mm
- ② **00103** Adapter, male Luer-lock and x-mas tree

CO₂ Filter




- A5663*** Filter, sterile, single use, for insufflation, large, 10 pcs.

2 to

For sterile filtration of the insufflation gas. Prevents possible contamination of the insufflation unit caused by backflow of body fluids.

Gas Preheater



- ① **WA58670A*** Gas preheater "GSH-2", 230 V, with heat exchanger
Delivery includes: Gas preheater, power cable, heat exchanger, adapter, 2 silicone tubings
- ② **WA58671A*** Heat exchanger "WISAP 7642HS", for WA58670A, autoclavable

Technical Data

Power supply	Voltage 230 V -
Frequency	50/60 Hz
Power consumption	55 W
Size	
Dimensions	150 (W) x 80 (H) x 170 (D) mm
Weight	2.2 kg
Classification	
Protection against electric shock class 1, type B	


- Provides constant body temperature under different flow conditions.
- The gas is heated over the complete heat exchanging tube length.
- Autoclavable heat exchanger for very low costs per procedure. Compatible to most available insufflators.

Surgery

Apolo

SOLTIVE Laser Fibers

- 34. suderi naimis su Soltive lazeriu



Ordering Information

Single-Use Fibers

Order No.	Description
EGTFL-FBX150S	150 micron single-use fiber, 5/box
EGTFL-FBX200S	200 micron single-use fiber, 5/box
EGTFL-FBX365S	365 micron single-use fiber, 5/box
EGTFL-FBX550S	550 micron single-use fiber, 5/box
EGTFL-FBX940S	940 micron single-use fiber, 5/box

Single-Use Ball-Tip Fibers

Order No.	Description
EGTFL-FBX150BS	150 micron single-use ball-tip fiber, 5/box
EGTFL-FBX200BS	200 micron single-use ball-tip fiber, 5/box

Accessories

Order No.	Description
EGTFL-AFC	SOLTIVE fiber cleaver
EGTFL-AFS150	SOLTIVE fiber stripper, 150 micron
EGTFL-AFS200	SOLTIVE fiber stripper, 200 micron
EGTFL-AFS365	SOLTIVE fiber stripper, 365 micron
EGTFL-AFS550	SOLTIVE fiber stripper, 550 micron
EGTFL-AFS940	SOLTIVE fiber stripper, 940 micron

SOLTIVE laser fibers are compatible with SOLTIVE SuperPulsed laser systems only.

¹ Compared to 200 μ fibers. Data on file. ² Data on file. Comparative fiber data collected with Cook 150. ³ Data on file. Comparative laser system data collected on Lumenis P120. ⁴ Data on file. Comparative fiber data collected with Cook 150, Lumenis 230 and EMPOWER 200 core diameter fibers.

Olympus reserves the right of errors, modification and changes of the service and/or product offerings.

OLYMPUS

OLYMPUS EUROPA SE & CO. KG
 Postbox 10 49 08, 20034 Hamburg, Germany
 Wendenstrasse 14-18, 20097 Hamburg, Germany
 Phone: +49 40 23773-0, Fax: +49 40 233765
 www.olympus-europa.com

pslo