



# AESCULAP® NEUROSURGERY

HAUPTKATALOG  
MAIN CATALOG

## INSTRUMENTS - INSTRUMENTE

### KERRISON NON-DETACHABLE BONE PUNCHES

KERRISON NICHT ZERLEGBARE KNOCHENSTANZEN

BONE  
KNOCHEN

JAW POSITION 130°, UPBITING  
MAULSTELLUNG 130°, NACH OBEN  
SCHNEIDEND

Length Länge	Width Breite	Footplate / Fußplatte					
		Standard		Standard		Thin / Dünnfuß	
		Jaw opening / Hub					
		Standard (mm)	Large / groß (mm)	Standard (mm)	Thin / Dünnfuß (mm)		
180 mm, 7"	1.0 mm	FF715R (8)	-	-	FF771R (8)		
	1.5 mm	FF638R (9)	-	-	FF645R (9)		
	2.0 mm	FF717R (9)	FF677R (15)		FF772R (9)		
	2.5 mm	FF639R (10)	-	-	FF646R (10)		
	3.0 mm	FF720R (10)	FF678R (15)	4.1	FF773R (10)		
	4.0 mm	FF724R (12)	FF679R (15)		FF769R (12)		
	5.0 mm	FF722R (12)	FF680R (15)		FF770R (12)		
	6.0 mm	FF726R (12)	-	-	-		
200 mm, 7 7/8"	1.0 mm	FF691R (8)	-	-	FF661R (8)		
	1.5 mm	FF649R (9)	-	-	FF658R (9)		
	2.0 mm	FF737R (9)	FF660R (15)		FF662R (9)		
	2.5 mm	FF657R (10)	-	-	FF659R (10)		
	3.0 mm	FF738R (10)	FF739R (15)		FF663R (10)		
	4.0 mm	FF727R (12)	FF745R (15)		FF664R (12)		
	5.0 mm	FF728R (12)	FF751R (15)		FF665R (12)		
	6.0 mm	FF729R (12)	FF753R (15)		-		
230 mm, 9"	1.0 mm	FF674R (8)	-	-	FF734R (8)		
	2.0 mm	FF682R (9)	-	-	FF746R (9)		
	3.0 mm	FF683R (10)	-	-	FF747R (10)		
	4.0 mm	FF684R (12)	-	-	FF748R (12)		
	5.0 mm	FF685R (12)	-	-	FF749R (12)		
280 mm, 11"	2.0 mm	FF686R (9)	-	-	FF666R (9)		
	3.0 mm	FF687R (10)	-	-	FF667R (10)		
	4.0 mm	FF688R (12)	-	-	FF668R (12)		
	5.0 mm	FF689R (12)	-	-	FF669R (12)		

JAW POSITION 130°, DOWNBITING  
MAULSTELLUNG 130°, NACH UNTEN  
SCHNEIDEND

Length Länge	Width Breite	Footplate / Fußplatte					
		Standard		Standard		Thin / Dünnfuß	
		Jaw opening / Hub					
		Standard (mm)	Large / groß (mm)	Standard (mm)	Thin / Dünnfuß (mm)		
180 mm, 7"	1.0 mm	FF711R (8)	-	-	FF781R (8)		
	2.0 mm	FF712R (9)	-	-	FF782R (9)		
	3.0 mm	FF713R (10)	-	-	FF783R (10)		
	4.0 mm	FF714R (12)	-	-	-		
	5.0 mm	FF725R (12)	-	-	-		

Ejector / Auswerfer

Non-detachable KERRISON punches don't have an ejector. / Alle nicht zerlegbaren Stanzen haben keinen Auswerfer.

Width / Breite (mm)

1.0  | 1.5  | 2.0  | 2.5  | 3.0  | 4.0  | 5.0  | 6.0