

## New valve housing: In-line

Pressure Range

### Valve System

<b>82-3816</b>	10mm H <sub>2</sub> O	Very Low	●
<b>82-3817</b>	40mm H <sub>2</sub> O	Low	●●
<b>82-3818</b>	70mm H <sub>2</sub> O	Medium	●●●
<b>82-3819</b>	100mm H <sub>2</sub> O	Medium High	●●●●
<b>82-3820</b>	130mm H <sub>2</sub> O	High	●●●●●

- 1 valve with integrated plastic connectors
- 1 ventricular catheter 14cm, silicone with stainless steel stylet
- 1 distal catheter 120cm, silicone
- 1 priming adaptor, plastic
- 1 right angled adaptor, plastic

### Valve System Unitised



<b>82-3806</b>	10mm H <sub>2</sub> O	Very Low	●
<b>82-3807</b>	40mm H <sub>2</sub> O	Low	●●
<b>82-3808</b>	70mm H <sub>2</sub> O	Medium	●●●
<b>82-3809</b>	100mm H <sub>2</sub> O	Medium High	●●●●
<b>82-3810</b>	130mm H <sub>2</sub> O	High	●●●●●

- 1 valve with integrated plastic connectors
- 1 ventricular catheter 14cm, silicone with stainless steel stylet
- 1 distal catheter 120cm, silicone and pre-connected
- 1 priming adaptor, plastic
- 1 right angled adaptor, plastic

### Valve only

<b>82-5471</b>	10mm H <sub>2</sub> O	Very Low	●
<b>82-5472</b>	40mm H <sub>2</sub> O	Low	●●
<b>82-5473</b>	70mm H <sub>2</sub> O	Medium	●●●
<b>82-5474</b>	100mm H <sub>2</sub> O	Medium High	●●●●
<b>82-5475</b>	130mm H <sub>2</sub> O	High	●●●●●

- 1 valve with integrated plastic connectors
- 1 priming adaptor, plastic



## New valve housing: In-line with SIPHONGUARD™

Pressure Range

### Valve System

po2.16.2

<b>82-3811</b>	10mm H <sub>2</sub> O	Very Low	●
<b>82-3812</b>	40mm H <sub>2</sub> O	Low	●●
<b>82-3813</b>	70mm H <sub>2</sub> O	Medium	●●●
<b>82-3814</b>	100mm H <sub>2</sub> O	Medium High	●●●●
<b>82-3815</b>	130mm H <sub>2</sub> O	High	●●●●●

- 1 valve with integrated plastic connectors
- 1 ventricular catheter 14cm, silicone with stainless steel stylet
- 1 distal catheter 120cm, silicone
- 1 priming adaptor, plastic
- 1 right angled adaptor, plastic

### Valve System Unitised

po2.16.2

<b>82-3821</b>	10mm H <sub>2</sub> O	Very Low	●
<b>82-3822</b>	40mm H <sub>2</sub> O	Low	●●
<b>82-3823</b>	70mm H <sub>2</sub> O	Medium	●●●
<b>82-3824</b>	100mm H <sub>2</sub> O	Medium High	●●●●
<b>82-3825</b>	130mm H <sub>2</sub> O	High	●●●●●

- 1 valve with integrated plastic connectors
- 1 ventricular catheter 14cm, silicone with stainless steel stylet
- 1 distal catheter 120cm, silicone and pre-connected
- 1 priming adaptor, plastic
- 1 right angled adaptor, plastic

### Valve only

po2.16.1

<b>82-5461</b>	10mm H <sub>2</sub> O	Very Low	●
<b>82-5462</b>	40mm H <sub>2</sub> O	Low	●●
<b>82-5463</b>	70mm H <sub>2</sub> O	Medium	●●●
<b>82-5464</b>	100mm H <sub>2</sub> O	Medium High	●●●●
<b>82-5465</b>	130mm H <sub>2</sub> O	High	●●●●●

- 1 valve with integrated plastic connectors
- 1 priming adaptor, plastic

