


Force-Displacement Graphing Software

Force Recorder Professional

- Data can be transmitted to plot the force-displacement (travel amount) graph easily.
- It is ideal for tactile analysis due to force transition is based on displacement.
- Graph can be drawn accurately and precisely due to the high sampling rate. (Mx. 2000Hz)
- You can switch between force-time and force-displacement based on your needs.
- The software program comes on a CD.




Basic function of Force Recorder Software	
Graph scaling function	The graph can be zoomed in/out, or scroll to check the details.
Statistical calculation	Maximum/minimum/average values are automatically calculated.
Comment function	Comments can be inserted on the graph to record the test condition.
Print	Graph, statistics value and comment can be printed out as report format.
Saving in CSV Format	Recorded data can be saved as CSV format.
Preview export function	Graph image and statistic data can be exported to various format. (e.g. Word, Excel and PDF)
Force gauge setting	The setting of force gauge can be changed via software.

Additional functions of Force Recorder Professional	
Display of displacement	Travel distance of force gauge can be recorded and displayed on software.
Graph overlay function	Graphs can be overlaid for easy comparison. (up to 5 graphs can be overlaid at once)
Trigger function	Recording can automatically start and stop according to force value, displacement, and external signals.
Add notes function	Comments can be placed anywhere on the graph.
Border line function	Lines can be drawn on the recorded graph at specific force/time as a judgement line.
Area select function	The statistics within the selected area are automatically calculated.

[Software Display]

<p>Real-time value display The display switches depending on the graphing mode.</p> <p style="text-align: center;">Force-Time mode</p> <p style="text-align: center;">Force-Displacement mode</p>	<p>Tabs Multiple files can be opened, and the screen shows the clicked tab.</p>
--	--



<p>Graph overlay function The graphs can be overlaid in Graph Overlay Tab. File names and graph colors are listed, and reference points can be set for easy comparison of graphs.</p>
--

Graph scaling function

The graph can be zoomed in/out and scrolled for analyzing.

Trigger function


Recording can automatically start and stop by the triggers such as force value, time etc.

The screenshot shows the Force Recorder Professional software interface. At the top, there is a menu bar with options: File, Edit, Display, CSV, Print, Settings, Help. Below the menu bar, there are control buttons for '0.00 N', '0.000 mm', 'ZERO', and 'ALL ZERO'. There are also 'START' and 'STOP' buttons, and a 'Waiting' status indicator. A 'Trigger Settings' button is highlighted with a red box and labeled 'OFF'. Below the control panel, there are tabs for 'Graphing', 'Graph Overlay 1', and 'Graph Overlay 2'. A toolbar with various graphing tools is visible. The main graph area displays Force (N) on the y-axis and Displacement (mm) on the x-axis, with several colored curves representing different data series. A 'Statistics' panel on the right side contains a 'Viewer' window showing a zoomed-in view of the graph, a table of statistics, and a 'Comment' section.

Statistics			
Recording Rate	T	0.0005	Sec
Max	F	29.23	N
	D	22.880	mm
Min	F	-13.29	N
	D	23.450	mm
Average	F	6.337	N
Data Count		13392	

[Graph viewer]

It shows the whole graph and the selected area.



[Graph statistics]

The maximum/minimum/average values are automatically calculated.



Statistics			
Recording Rate	T	0.0005	Sec
Max	F	29.23	N
	D	22.880	mm
Min	F	-13.29	N
	D	23.450	mm
Average	F	6.337	N
Data Count		13392	



[Comment]

Comments can be inserted on the graph to record the test condition.

The screenshot shows the 'Comment' window, which is a text input area for recording test conditions. It includes a 'Comment' label and a large text area for input.

[Main Functions]

Force-Displacement(Time) Graphing	Graph Edit
<p>1. The recording can start/stop by simply click the buttons.</p>  <p>(START/STOP buttons)</p> <p>2. Force transition can be viewed clearly by 2 different displays which show the whole graph and current force and displacement values.</p>  <p>3. Recording can automatically start and stop by setting the trigger such as force value, time etc. (Trigger function) e.g., The software will start recoding when force reaches 1N, and stop after 10 sec.</p>	<p>1. It is possible to cut out and save only the necessary area of a recorded graph. And the new statistical value is automatically calculated. (Area select function)</p> <p>2. Comments can be added at a specific point on the graph. (Add notes function)</p> <p>3. Border lines can be drawn on the graph with any force value and displacement/time. (Border line function)</p>  <p>(Screen after edited)</p>
Viewing Graph	Print
<p>1. The recorded graph can be zoomed in/out or scrolled easily to check the details. (Graph scaling function)</p> <p>2. The graphs can be overlaid for easy comparison. (up to 5 graphs can be overlaid at once)</p>	<p>1. The graph, statistical values (maximum/minimum/average), and comments can be printed in the report format.</p> <p>2. The selected area of the graph can be enlarged and printed.</p>

Output Functions	
<p>Saving in CSV Format</p> <ul style="list-style-type: none"> - Recorded graph data can be saved as CSV format. - It is also possible to add new data to an existing CSV file. 	<p>Preview export function</p> <ul style="list-style-type: none"> - Graph image and statistic data can be exported to Word, Excel and PDF format. - Graph images can be pasted into other files.
	

Main Functions Comparison			
Version	Light	Standard	Professional
Feature	Graphing only	With editing functions	Force-displacement graphing
Graphing	Force-time	Force-time	Force-time Force-displacement
Data transferring speed (Max)	2000 data/sec	2000 data/sec	2000 data/sec
Recording data point (Max)	7.2 million	7.2 million	7.2 million
Displacement output	N/A	N/A	√
Graph overlaying function	N/A	√	√
Trigger function	N/A	√	√
Add notes function	N/A	√	√
Border line function	N/A	√	√
Area select function	N/A	√	√
Graph scaling	√	√	√
Statistical calculation	√	√	√
Comment function	√	√	√
Print	√	√	√
Saving in CSV Format	√	√	√
Preview export function (PDF/Word/Excel)	√	√	√
Force gauge setting	√	√	√

* For further information of Light and Standard version, refer to Force Recorder Light and Standard specification.

Specification	
Model	Force Recorder Professional
Operating environment	OS: Windows 8.1/10/11
Hardware	CPU: 1GHz or higher Memory: 2GB or more Hard disk: 10GB (Data storage area) more
Plat form	.NET Framework4.8 later
Image size	Resolution 1024*768 pixel more
Compatible devices	ZTA series, HTGA series, DTXA series, eZT, FA Plus2/eFA Plus2 (Available for drawing both force-time and force-displacement graph.) *Required to be connected with a linear scale/an angle meter kit or a build-in linear scale (-FA option) by the designated cable.
	ZTS series, HTGS series, DTXS series (Available only for drawing force-time graph.)


[Gauges available for drawing force-displacement graph] *

Force-Displacement and Force-Time graph		
Digital Force Gauge ZTA series	Sensor Interchangeable Amplifier eZT	Desk Type Load Cell Amplifier FA Plus2/eFA Plus2
For Torque-Angle and Torque-Time graph		
Handy Type Torque Gauge HTGA series	Screw Cap Torque Tester DTXA series	


* To be able to draw a force-displacement/torque-angle graph, a linear scale/angle meter or a build-in test stand is required.

Related Products

Force Displacement Analysis Unit FSA series



1



2, 3, 4, 5

This unit includes the necessary items for performing force-displacement measurement.


Set Content:

1. Software Force Recorder Professional
2. Force Gauge ZTA series
3. Test Stand with linear scale
4. Cable
5. Standard Attachment


* Optional attachment GT-30 is not included

FSA-1KE series

Torque-Angle Analysis Unit TAA series



1



2, 3, 4, 5

This unit includes the necessary items for performing torque-angle measurement.

Set Content:

1. Software Force Recorder Professional
2. Screw Cap Torque Tester DTXA series
3. Test Stand with angle meter
4. Cable
5. Standard Attachment

TAA-MTS-TB series

* Refer to specifications of the individual product for details.

Related Software	
Downloadable Graphing Software*1 : Force Recorder Next Standard / Professional	
	<ul style="list-style-type: none"> - Professional version is for force-time graphs and force-displacement graphs. - Standard version is for force-time graphs. - Test condition preset functions increase efficiency of recording and analyzing measurement results. - Various data editing functions such as up to 10-graph overlaying enable analyzing measurement result. - Annotation functions are useful for recording the details of measurement. - The Print Command allows users to output of measurement data as PDF/Word, Excel, and images and drawing up reports easily - Software program online-updating and additional function downloading are available on the user support site, IMADA Connected.

*1 To use this product, user & product registration on IMADA Connected is required and please note that only Next Series products are available for the product registration. An Internet connection is required in this process.

* Some specification such as operating environment is different from Downloadable version and CD version.

* Please refer to the individual specification sheets for details.

[Custom-made]

We can offer additional functions or modifying software to improve data management method and measurement efficiency according to your needs. Contact us for details.

Examples:

Function	Description
Pass/Fail Judgment	The software will judge the test result according to the set value.
Automatic Capture Functions	The software will automatically capture the needed graph based on the set values.
CSV Auto Save	The CSV file will be saved automatically after the measurement.
Trigger One-Touch Setting	The trigger function can be activated with ease.

[Cautions]

- Information in this document is subject to change without prior notice.
- This document is product descriptions and handling precautions, and do not guarantee various characteristics or safety.
- This product is designed for force measurement purpose only.
- Do not copy and use this content without authorization.
- A force gauge (sold separately) is required to use this product.
- This product is protected by Universal Copyright Convention and Japanese Copyright Act.
- Returns are not acceptable. Check the specification, working conditions and operating environment before purchase.

IMADA CO., LTD.

99, Jinnoshinden-Cho, Aza, Kanowari, Toyohashi,
Aichi 441-8077, JAPAN
Tel: +81-(0)532-33-3288
Fax: +81-(0)532-33-3866
E-mail: info@forcegauge.net
Website: <https://www.forcegauge.net/en/>



Visit our website for more information on a wide range of product specifications, measurement applications and videos.