



# Office Organisation



## Fineliner 1700 VARIO

edding.

For fine and precise writing on paper surfaces.

- Metal-mounted round tip
- Water-based ink

Rubber grip, flexible and slip-resistant for a comfortable writing experience. The cap can be stored at the end of the barrel to avoid the risk of loss. The practical clip prevents the pen from rolling away and can be attached to clothing and objects.

Type	Colour	Line width (mm)	Art. No.	Pack Qty.
1700 VARIO	black	0.5	1AE2.1	10 unit(s)
1700 VARIO	red	0.5	1AE3.1	10 unit(s)
1700 VARIO	blue	0.5	1AE4.1	10 unit(s)



## Laboratory markers Securiline®

ROTH SELECTION.

Permanent marker for writing on virtually all surfaces made of glass, metal and most plastics. Length 135 mm.

- Even writes on wet or cold surfaces
- Waterproof, even during autoclaving
- Fast-drying
- Can be wiped off high-gloss surfaces

Colour	Line width (mm)	Art. No.	Pack Qty.
black	1	3083.2	10 unit(s)
blue	1	3084.2	10 unit(s)
red	1	3085.2	10 unit(s)

### Set

4 x black, 4 x blue, 4 x red

Colour	Line width (mm)	Art. No.	Pack Qty.
assorted colours	1	1701.1	12 unit(s)



## Laboratory markers Sharpie®

ROTH SELECTION.

Waterproof permanent marker for glass, metal, porcelain or similar surfaces. Fast-drying.

Colour	Version	Line width (mm)	Art. No.	Pack Qty.
black	Single tip	1	KN09.1	12 unit(s)

### Set

Assorted colours (black, blue, purple, bordeaux, light blue, light green, turquoise, orange).

Colour	Version	Line width (mm)	Art. No.	Pack Qty.
assorted colours	Double tip	1 / 0,5	XT85.1	8 unit(s)



## Laboratory markers ink pen set

Faber-Castell.

Permanent, waterproof, fast-drying. With special rubber. For writing on virtually all surfaces.

Assorted colours (2 x black, 2 x green, 2 x blue, 2 x red).

Type	Colour	Line width (mm)	Art. No.	Pack Qty.
Multimark 1523	assorted colours	0,4	0883.1	1 set



## Laboratory markers stericlin® sterilisation-resistant

ROTH SELECTION.

For labelling disposable items such as sterile barrier systems, adhesive tapes and labels. Only label transparent packaging on the film side and outside the area of the filling material.

Colour	Line width (mm)	Art. No.	Pack Qty.
black	0,6	HXE3.1	10 unit(s)
blue	0,6	HXE4.1	10 unit(s)