

## GC Pattern Resin LS



### Low Shrinkage Modelling Resin

The proven modelling resin for making all types of custom attachments, fixations, implant abutments or resin dies for electroforming technique.

### PACKAGES

GC Pattern Resin LS	
335201	1-1 Pack (100 g powder, 105 ml liquid, 2 mixing cups, 1 brush N°4 & 1 pipette)
335202	100 g powder
335204	1 kg powder
335203	105 ml liquid
335205	262 ml liquid
001416	Brushes N°4, 10 pcs

### CHARACTERISTICS & BENEFITS

- Minimal shrinkage and easy-to-trim for perfect adaptation and reproduction
- High hardness and strength
- High stability even for thin layers
- Burns out without residue resulting in very clean casting surfaces

### HOW TO USE

GC Pattern Resin LS is specially developed for the brush technique.

## GC Inlay Wax SOFT, MEDIUM & HARD



### Dental Inlay Casting Wax

Modelling wax for all kinds of restorations with excellent plasticity and low deformation during removal from the model.

### PACKAGES

GC Inlay Wax	
SOFT	
001157	60 sticks (Violet)
001159	60 sticks (Grey)
001154	40 g tin (Violet)
001156	40 g tin (Grey)
MEDIUM	
001086	60 sticks (Grey)
001084	60 sticks (Green)
001083	40 g tin (Grey)
001081	40 g tin (Green)
HARD	
001162	40 g tin (Grey)
001160	40 g tin (Green)

### CHARACTERISTICS & BENEFITS

- Excellent plasticity
- High modelling ability, low shrinkage
- Burns out without residues
- Smooth castings

## GC Ostron



### Self-Curing Resin For Custom Trays

Acrylic resin for manufacturing custom trays, base plates and bite-registration.

### PACKAGES

GC Ostron P/L	
000615	Blue-Transparent, 1 kg powder
000605	Clear (Pink-Transparent), 1 kg powder
000354	250 ml liquid

### CHARACTERISTICS & BENEFITS

- Time-saving
- Excellent adaptability, but does not stick
- Ample working time
- Smooth shiny surface and high dimensional stability
- Easy to trim